4000VAC isolation test voltage, EFD25, flyback transformer



FEATURES

- 85 ~ 264VAC wide input voltage range
- EFD25 Bobbin
- Meets UL/EN 62368 standards

TTLHE25-20BxxD transformer series feature with 4000VAC primary to secondary isolation, an operating ambient temperature range of -40 $^{\circ}$ C ~ +110 $^{\circ}$ C. It can be used with our control IC SCM1710ASA to achieve flyback power supply design with wide input volatge range and various protection functions and superior EMI performance.

Selection Guide							
Part No.	Input Voltage (VAC)	Output Voltage (VDC)	Output Current (mA)	Auxiliary Voltage (VDC)	Auxiliary Current (mA)	Typical Power (W)	Typical Operating Frequency (kHz)
TTLHE25-20B12D	85 ~ 264	12	2100	19.68	20	25	65

Note: Refer to Schematic for pins and phase points of the transformers.

Electrical Specifications							
Inductance [®] (uH)			$DCR(m\Omega)$ Typ.			K	
Part No.	Input Inductance	Leakage Inductance Max.	N1	N2	N3	(Flux Density Factor) (Gauss/A)	
TTLHE25-20B12D	1440.00±10%	100.00	782	32	820	3143	

Notes: ①The test signal of the inductance are 10kHz and 100mV, test the leakage inductance of N1 based on N2 and N3 are shorted;

②To ensure the transformer will not saturate in all of the applications and conditions, the peak flux density(Bm) should remain below 3000Gauss. Use the following formula to calculate the peak flux density: Bm=K*lpk, lpk stands for the peak current of input, which unit is A;

③ Approximate transformer core loss(Pcv) can be calculated as following formula: Pcv=3.9E-14*f^{1.82*} \triangle B^{2.59}, the unit of Pcv is W, f stands for operating frequency, which unit is kHz, \triangle B is the operating flux density, which unit is Gauss. \triangle B can be calculated as: \triangle B=K* \triangle I.

Genera	I Specification	ons				
ltem		Operating Conditions	Min.	Тур.	Max.	Unit
looletion	N1, N3 to N2	Electric Strength Test for 1 minute, leakage current <5mA	4000			VAC
Isolation N1 to N3		Electric Strength Test for 1 minute, leakage current < 1 mA	1000	-	-	VDC
Operating 1	「emperature®		-40		+110	°C
Storage Ten	nperature [®]		-40	-	+110	
Storage Hur	midity	Non-condensing	-		95	%RH
Soldering Temperature		Wave-soldering	260 ± 5°C; time: 5 - 10s			
		Manual-welding	360 ± 10°C; time: 3 - 5s			
Creepage I	Distance		7.0	-	_	
Clearance			6.4	_	-	mm
Motos (1)The	a tampagetura of the	transform or (analsiant plus toponorative visa) about a la partition the analysis	in a tomonorat			

Notes: ①The temperature of the transformer (ambient plus temperature rise) should be within the operating temperature range;

②The storage temperature of the transformer only.


The isolation strap of the peripheral is designed to meet the clearance and creepage distance.

Mechanical Specifications					
Weight	TTLHE25-20B12D	25.20g (Typ.)			


MORNSUN®

MORNSUN GUANGZHOU SCIENCE & TECHNOLOGY CO.,LTD.

Material Certification			
Material	UL No.		
Bobbin	E41429		
Tape	E17385		
Wire 1	E196072		
Wire 2	E234867		
Wire 3	E206440		
Varnish	E317427		
Glue	E250719		



Dimensions and Recommended Layout





Notes:

- 1. For additional information on Product Packaging please refer to www.mornsun-power.com. Packaging bag number: 58220096;
- 2. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75%, 10kHz and 100mV
- 3. All index testing methods in this datasheet are based on our company corporate standards;
- 4. We can provide product customization service, please contact our technicians directly for specific information;
- 5. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

Mornsun Guangzhou Science & Technology Co., Ltd.

Address: No. 5, Kehui St. 1, Kehui Development Center, Science Ave., Guangzhou Science City, Huangpu District, Guangzhou, P. R. China
Tel: 86-20-38601850 Fax: 86-20-38601272 E-mail: info@mornsun.cn www.mornsun-power.com

MORNSUN®

MORNSUN GUANGZHOU SCIENCE & TECHNOLOGY CO.,LTD.