3000VAC isolation test voltage, EPC13, flyback transformer



### **FEATURES**

- 85 ~ 305VAC wide input voltage range
- EPC13 Bobbin
- Meets UL/EN 62368 standards

TILS03-15BxxT transformer series feature with 3000VAC primary to secondary isolation, an operating ambient temperature range of -40°C to +110°C. It can be used with our control IC SCM1702ASA to achieve flyback power supply design with wide input volatge range and various protection functions and superior EMI performance.

Selection Guide							
Part No.	Input Voltage (VAC)	Output Voltage (VDC)	Output Current (mA)	Auxiliary Voltage (VDC)	Auxiliary Current (mA)	Typical Power (W)	Typical Operating Frequency (kHz)
TTLS03-15B05T	85 ~ 305	5	600	18.65	20	3	65
TTLS03-15B12T	85 ~ 305	12	250	17.76	20	3	65
Note: Defer to Schematic for nine and phase points of the transformers							

Note: Refer to Schematic for pins and phase points of the transformers.

Electrical Specifications						
Part No.	Inductance <sup>®</sup> (uH)		DCR(mΩ) Typ.			K
	Input Inductance	Leakage Inductance Max.	N1	N2	N3	(Flux Density Factor) (Gauss/A)
TTLS03-15B05T	952.56±10%	80.00	3580	40	1620	5911
TTLS03-15B12T	952.56±10%	80.00	3580	326	1500	5911

Notes: ①The test signal of the inductance are 10kHz and 100mV, test the leakage inductance of N1 based on N2 and N3 are shorted;

②To ensure the transformer will not saturate in all of the applications and conditions, the peak flux density(Bm) should remain below 3000Gauss. Use the following formula to calculate the peak flux density: Bm=K\*lpk, lpk stands for the peak current of input, which unit is A;

® Approximate transformer core loss(Pcv) can be calculated as following formula: Pcv=3.9E-14\*f1.82\*  $\triangle$  B2.59, the unit of Pcv is W, f stands for operating frequency, which unit is kHz,  $\triangle$ B is the operating flux density, which unit is Gauss.  $\triangle$ B can be calculated as:  $\triangle$ B=K\* $\triangle$ I.

General	<b>Specification</b>	ns				
ltem		Operating Conditions	Min.	Тур.	Max.	Unit
N1, N3 to N2		Electric Strength Test for 1 minute, leakage current <5mA	3000			VAC
Isolation	N1 to N3	Electric Strength Test for 1 minute, leakage current < 1 mA	1000			VDC
Operating Te	Operating Temperature <sup>0</sup> -40		+110	°C		
Storage Temperature®			-40	_	+110	°C
Storage Hun	nidity	Non-condensing	95 %R		%RH	
Reflow Solds	ering Temperature®		Peak temp. $\leq$ 245°C, maximum duration ti $\leq$ 60s over 217°C.		uration time	
Creepage Distance			5.7	-	-	
Clearance			5.7	_	_	mm

Notes: ①The temperature of the transformer (ambient plus temperature rise) should be within the operating temperature range;

②The storage temperature of the transformer only;

3We suggest that times of reflow soldering should not exceed twice.


(4) The isolation strap of the peripheral is designed to meet the clearance and creepage distance.

Mechani	cal Specifications	
Weight	TTLS03-15B05T	2.70c (firm.)
	TTLS03-15B12T	3.70g (Typ.)


**MORNSUN®** 

MORNSUN Guangzhou Science & Technology Co., Ltd.


Material Certit	ication	
Material	UL No.	
Bobbin	E54705	
Tape	E17385	
Wire 1	E234867	
Wire 2	E206440	
Varnish	E317427	
Glue	E250719	




## TTLS03-15B05T Dimensions and Recommended Layout



### TTLS03-15B12T Dimensions and Recommended Layout



### Tape and Reel Info



#### Note:

- 1. For additional information on Product Packaging please refer to www.mornsun-power.com. Packaging bag number: 58220092;
- 2. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta= $25^{\circ}$ C, humidity<75%, 10kHz and 100mV;
- 3. All index testing methods in this datasheet are based on our company corporate standards;
- 4. We can provide product customization service, please contact our technicians directly for specific information;
- 5. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

# Mornsun Guangzhou Science & Technology Co., Ltd.

Address: No. 5, Kehui St. 1, Kehui Development Center, Science Ave., Guangzhou Science City, Huangpu District, Guangzhou, P. R. China Tel: 86-20-38601850 Fax: 86-20-38601272 E-mail:info@mornsun.cn www.mornsun-power.com

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.