




Mounting aid RL28-GLASS-C


- Simple and fast mounting



Replacement glass



Dimensions



Technical Data

General specifications

Accessories provided	M4 x 8 mm thumb screw
----------------------	-----------------------

Mechanical specifications

Material	glass
----------	-------


Suitable series

Series	RL28 RL29
--------	--------------

Step 1

- Push lens into the lip on the housing as shown.
- Rotate lens into position as shown.

Caution: Glass lens is fragile, handle with care



Step 2

- After lens has been rotated into it's correct position. Secure it as shown below.

Caution: Do not over tighten, glass lens is very fragile.

